

25T8C-120V



Description

120V 25W T-8 Candelabra Base

Specifications

Bulb Type	T-8
Base Type	Candelabra Screw (E12)
Filament	C-7A
Special Desc	
MOL in/mm	2.63/66.8
MOD in/mm	1.04/26.4
Volts	120
Watts	25
Amps	0.21
Lumens	180
Avg Life	1,500
Photo No	101
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335