

40A15-130V



Description

40W 130V A-15 Medium Base

Specifications

Bulb Type	A-15
Base Type	Medium Screw (E26)
Filament	C-2V
Special Desc	At 120V - 35 Watts, 265 Lumens, 3,750 Hrs, 2550 CCT, 7.57 LPW
MOL in/mm	3.5/89
MOD in/mm	1.9/48
LCL in/mm	2.38/60.3
Volts	130
Watts	40
Lumens	350
CT deg K	2600
Avg Life	1,500
Photo No	1
Coating	Clear
Lumens per Watt	8.75000

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335