



**Description**

6V 4.5A S-11 E-14 Prefocus Special Flange

Specifications	
<b>Bulb Type</b>	S-11
<b>Base Type</b>	E14 w/ Special Flange (P44s)
<b>Filament</b>	C-6
<b>MOL in/mm</b>	2.52/64
<b>MOD in/mm</b>	1.38/35
<b>Volts</b>	6
<b>Watts</b>	27
<b>Watts Amps</b>	(4.5)
<b>Amps</b>	4.5
<b>Lumens</b>	360
<b>Avg Life</b>	100
<b>Type Use</b>	Slit Lamp
<b>Photo No</b>	337

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335