

# 60PAR38/H/SP-120V



**Description**

120V 60W Spot EikON PAR38 Medium Base

Specifications	
<b>Bulb Type</b>	PAR 38
<b>Base Type</b>	Medium Screw (E26)
<b>Filament</b>	CC-8
<b>Special Desc</b>	120V 60W Spot EikON PAR38 Medium Base
<b>MOL in/mm</b>	5.2/132
<b>MOD in/mm</b>	4.8/122
<b>Volts</b>	120
<b>Watts</b>	60
<b>Amps</b>	0.5
<b>Lumens</b>	1070
<b>CT deg K</b>	3000
<b>Avg Life</b>	1,500
<b>Photo No</b>	940
<b>Approx Initial Max Beam CP</b>	4600
<b>Beam Angle</b>	15

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335