



70PAR38/H/SP-120V

**Description**

120V 70W Spot EiKON PAR38 Medium Base

Specifications	
Bulb Type	PAR 38
Base Type	Medium Screw (E26)
Filament	CC-8
Special Desc	120V 70W Spot EiKON PAR38 Medium Base
MOL in/mm	5.2/132
MOD in/mm	4.8/122
Volts	120
Watts	70
Amps	0.58
Lumens	1305
CT deg K	3000
Avg Life	1,500
Photo No	940
Approx Initial Max Beam CP	5400
Beam Angle	15

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335