



Description

5V .115A T1-3/4 Bipin Base

Specifications

Bulb Type	T-1 3/4
Base Type	Bi-Pin .125 (G3.17)
Filament	C-2R
MOL in/mm	0.63/16.0
MOD in/mm	0.23/5.9
Volts	5
Amps	0.115
Lumens	1.89
Avg Life	40,000
Photo No	40

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335