



**Description**

28V .04A T1-3/4 Bipin Base

**Specifications**

<b>Bulb Type</b>	T-1 3/4
<b>Base Type</b>	Bi-Pin .125 (G3.17)
<b>Filament</b>	C-2F
<b>MOL in/mm</b>	0.60/15.2
<b>MOD in/mm</b>	0.23/5.9
<b>LCL in/mm</b>	0.50/12.7
<b>Volts</b>	28
<b>Amps</b>	0.04
<b>Lumens</b>	1.89
<b>Avg Life</b>	10,000
<b>Photo No</b>	40

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335