



**Description**

12.8V 50W Axial Filament T-4 SC Bayonet Base Halogen

Specifications	
<b>Bulb Type</b>	T-4
<b>Base Type</b>	SC Bayonet (BA15s)
<b>Filament</b>	C-8
<b>Special Desc</b>	Halogen. Caution - Do Not Use in Plastic Sockets.
<b>MOL in/mm</b>	2.50/63.5
<b>MOD in/mm</b>	0.48/12.2
<b>Volts</b>	12.8
<b>Watts</b>	50
<b>Amps</b>	3.91
<b>Lumens</b>	1355
<b>Avg Life</b>	200
<b>Photo No</b>	80

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335