



Description

12V 25/25W T-6 DC Bayonet Special Flange Base

Specifications

Bulb Type	T-6
Base Type	Double Contact Flanged (PX15d)
Filament	C-2V/C-2V
Special Desc	Design volts is 13/13
MOL in/mm	1.85/47.0
MOD in/mm	0.79/20.1
LCL in/mm	0.79/20.0
Volts	12/12
Watts	25/25
Amps	2.08/2.08
Lumens	453/453
Avg Life	100/100
Photo No	113

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335