



Description

12V 20W 38 Deg. MR16 GU5.3 Base

Specifications	
Bulb Type	MR16
Base Type	GU5.3
Filament	C-8
Special Desc	Dichroic Reflector
MOL in/mm	1.81/46.0
MOD in/mm	2.00/50.8
Volts	12
Watts	20
Watts Amps	20
Amps	1.67
CT deg K	2950
Avg Life	4,000
Type Use	Display 38
Photo No	241
Poss Sub	ESX
Approx Initial Max Beam CP	460
Beam Angle	38
Beam Description	Flood
Common Code	Q20MR16/FL
Burning Position	Any

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335