



Description

LED Area Street Light Sq Pole Fixture Nichia 219 50W
5000K Type V Bronze 120-277V

Specifications	
Volts	120~277 VAC
Watts	50
Ambient Operating Temp Range	-40°C (-40°F) to 55°C (131°F)
Lumens	5000
CT deg K	5000
Photo No	931
Approvals	ETL, LM79, LM80

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335