



Description

130V 50W T-8 DC Bayonet Base

Specifications

Bulb Type	T-8
Base Type	DC Bayonet (BA15d)
Filament	CC-13
MOL in/mm	3.13/79.4
MOD in/mm	1.00/25.4
LCL in/mm	1.38/34.9
Volts	130
Watts	50
Lumens	775
CT deg K	2875
Avg Life	50
Type Use	Acuity (Eye Chart) Projection
Photo No	202
Poss Sub	CAC
Burning Position	BD

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335