



**Description**

130V 50W T-4 Halogen DC Bayonet Base

**Specifications**

<b>Bulb Type</b>	T-4
<b>Base Type</b>	DC Bayonet (BA15d)
<b>Filament</b>	C-2V
<b>MOL in/mm</b>	2.36/60
<b>MOD in/mm</b>	0.53/13.5
<b>LCL in/mm</b>	1.38/34.9
<b>Volts</b>	130
<b>Watts</b>	50
<b>Watts Amps</b>	50
<b>Amps</b>	0.38
<b>Lumens</b>	800
<b>CT deg K</b>	2875
<b>Avg Life</b>	500
<b>Type Use</b>	Acuity (Eye Chart) Projection
<b>Photo No</b>	794
<b>Poss Sub</b>	CAC
<b>Burning Position</b>	BD

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335