



Description

100W EDX17 Universal Protected Medium Base Coated 4000K 92+ CRI Ceramic Metal Halide

Specifications

Bulb Type	EDX-17
Base Type	Medium Screw (E26)
Special Desc	Magnetic Ballasts Not Recommended. See instruction's wiring diagram.
MOL in/mm	5.43/138
Watts	100
CT deg K	4000
Avg Life	20,000
Photo No	807
ANSI Ballast	M140/M90/O
CRI	92+
Burning Position	Universal
Approx Initial Lumens	7500
Fixt Rqmt	Open
Coating	Coated
Approvals	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335