



# CMP70/C/MP/3K

**Description**

70W EDX17 Universal Protected Medium Base Coated 3000K 90+ CRI Ceramic Metal Halide

Specifications	
<b>Bulb Type</b>	EDX-17
<b>Base Type</b>	Medium Screw (E26)
<b>Special Desc</b>	Magnetic Ballasts Not Recommended. See instruction's wiring diagram.
<b>MOL in/mm</b>	5.43/138
<b>Watts</b>	70
<b>CT deg K</b>	3000
<b>Avg Life</b>	16,000
<b>Photo No</b>	805
<b>ANSI Ballast</b>	M139/M98/M143/O
<b>CRI</b>	90+
<b>Burning Position</b>	Universal
<b>Approx Initial Lumens</b>	5400
<b>Fixt Rqmt</b>	Open
<b>Coating</b>	Coated

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335