



CMP70/C/MP/4K

**Description**

70W EDX17 Universal Protected Medium Base Coated 4000K 92+ CRI Ceramic Metal Halide

Specifications

| | |
|------------------------------|--|
| Bulb Type | EDX-17 |
| Base Type | Medium Screw (E26) |
| Special Desc | Magnetic Ballasts Not Recommended. See instruction's wiring diagram. |
| MOL in/mm | 5.43/138 |
| Watts | 70 |
| CT deg K | 4000 |
| Avg Life | 20,000 |
| Photo No | 805 |
| ANSI Ballast | M139/M98/M143/O |
| CRI | 90+ |
| Burning Position | Universal |
| Approx Initial Lumens | 5200 |
| Fixt Rqmt | Open |
| Coating | Coated |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335