



**Description**

70W T6 G12 Base 3000K 90 CRI Ceramic Metal Halide

Specifications	
<b>Bulb Type</b>	T-6
<b>Base Type</b>	G12
<b>Special Desc</b>	UV Block Quartz Glass. Magnetic Ballasts Not Recommended. See instruction's wiring diagram.
<b>MOL in/mm</b>	4.33/110
<b>LCL in/mm</b>	2.05/52
<b>Watts</b>	70
<b>CT deg K</b>	3000
<b>Avg Life</b>	15,000
<b>Photo No</b>	696
<b>ANSI Ballast</b>	M139/M98/M143/E
<b>CRI</b>	90
<b>Burning Position</b>	Universal
<b>Approx Initial Lumens</b>	7200
<b>Approx Mean Lumens</b>	5980
<b>Fixt Rqmt</b>	Enclosed

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335