



**Description**

13W Duo-Tube 4100K GX23 Base Compact Fluorescent

Specifications	
<b>Bulb Type</b>	T-4
<b>Base Type</b>	GX23
<b>MOL in/mm</b>	7.3/185
<b>Watts</b>	13
<b>CT deg K</b>	4100
<b>Avg Life</b>	10,000
<b>Photo No</b>	308
<b>CRI</b>	82
<b>Approx Initial Lumens</b>	825
<b>Approx Mean Lumens</b>	710
<b>Approvals</b>	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335