



**Description**

21V 150W MR16 GX5.3 Base

**Specifications**

<b>Bulb Type</b>	MR16
<b>Base Type</b>	GX5.3
<b>Filament</b>	CC-6
<b>Special Desc</b>	Dichroic Reflector
<b>MOL in/mm</b>	1.75/44.5
<b>MOD in/mm</b>	2.00/50.8
<b>Volts</b>	21
<b>Watts</b>	150
<b>Watts Amps</b>	150
<b>Amps</b>	7.14
<b>CT deg K</b>	3350
<b>Avg Life</b>	40
<b>Type Use</b>	8mm/Printer
<b>Photo No</b>	133
<b>Poss Sub</b>	EKE
<b>Burning Position</b>	BDTH

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335