



# EXN-FG-GU10-130V

**Description**

130V 50W 38 Deg. Flood MR16 GU10 Base

Specifications	
<b>Bulb Type</b>	MR16
<b>Base Type</b>	GU10
<b>Filament</b>	8-Style
<b>Special Desc</b>	Dichroic Reflector w/ Front Glass
<b>MOL in/mm</b>	2.20/56
<b>MOD in/mm</b>	2.20/50.8
<b>Volts</b>	130
<b>Watts</b>	50
<b>Watts Amps</b>	50
<b>Amps</b>	0.38
<b>CT deg K</b>	2700
<b>Avg Life</b>	3,500
<b>Photo No</b>	577
<b>Approx Initial Max Beam CP</b>	900
<b>Beam Angle</b>	38
<b>Beam Description</b>	Flood
<b>Burning Position</b>	Any

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335