



**Description**

24W 4100K T5 85 CRI G5 Base High Output

Specifications	
<b>Bulb Type</b>	T-5
<b>Base Type</b>	G5
<b>Special Desc</b>	Hi Output, Programmed Start
<b>MOL in/mm</b>	22/559
<b>Watts</b>	24
<b>CT deg K</b>	4100
<b>Photo No</b>	316
<b>CRI</b>	85
<b>Approx Initial Lumens</b>	1750
<b>Approx Mean Lumens</b>	1625
<b>Life 3hr Start</b>	25,000
<b>Life 12hr Start</b>	35,000
<b>Approvals</b>	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335