



# F54T5/HO/850



Description

54W 5000K T5 85 CRI G5 Base High Output

Specifications	
Bulb Type	T-5
Base Type	G5
Special Desc	Hi Output, Programmed Start
MOL in/mm	46/1169
Watts	54
CT deg K	5000
Photo No	316
CRI	85
Approx Initial Lumens	4850
Approx Mean Lumens	4500
Life 3hr Start	25,000
Life 12hr Start	35,000
Approvals	TCLP Compliant

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335