



Description

12V 65W 12 Deg. Narrow Spot MR16 GU5.3 Base

Specifications

Bulb Type	MR16
Base Type	GU5.3
Filament	C-8
Special Desc	Faceted Reflector
MOL in/mm	1.81/46.0
MOD in/mm	2.00/50.8
Volts	12
Watts	65
Watts Amps	65
Amps	5.42
CT deg K	3050
Avg Life	4,000
Type Use	Display 12
Photo No	241
Poss Sub	EYF
Approx Initial Max Beam CP	11,500
Beam Angle	12
Beam Description	Narrow Spot
Common Code	Q65MR16/NSP
Burning Position	Any

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335