



**Description**

12V 35W 18 Deg. Spot MR16 GU5.3 Base

Specifications	
<b>Bulb Type</b>	MR16
<b>Base Type</b>	GU5.3
<b>Filament</b>	C-8
<b>Special Desc</b>	Dichroic Reflector w/ Front Glass
<b>MOL in/mm</b>	1.99/50.5
<b>MOD in/mm</b>	2.00/50.8
<b>Volts</b>	12
<b>Watts</b>	35
<b>CT deg K</b>	3050
<b>Avg Life</b>	4,000
<b>Type Use</b>	Display 18
<b>Photo No</b>	242
<b>Approx Initial Max Beam CP</b>	2800
<b>Beam Angle</b>	18
<b>Beam Description</b>	Spot
<b>Common Code</b>	JR12V35W-CG

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335