



Description

12V 12W 10 Deg. Narrow Spot MR11 GU4 Base

Specifications

Bulb Type	MR11
Base Type	GU4
Filament	C-8
Special Desc	Dichroic Reflector
MOL in/mm	1.38/35.0
MOD in/mm	1.39/35.3
Volts	12
Watts	12
Watts Amps	12
Amps	1
CT deg K	2900
Avg Life	2,000
Type Use	Display 10
Photo No	236
Approx Initial Max Beam CP	1300
Beam Angle	10
Beam Description	Spot
Common Code	Q12MR11/NSP
Burning Position	Any

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335