

IR53PAR30LN/SP



Description

120V 53W Spot EiKON IR PAR30 Long Neck Medium Base

Specifications

Bulb Type	PAR 30LN
Base Type	Medium Screw (E26)
Filament	CC-8
MOL in/mm	4.76/121
MOD in/mm	3.74/95
Volts	120
Watts	53
Lumens	930
CT deg K	2750
Avg Life	4,000
Photo No	959
Approx Initial Max Beam CP	12000
Beam Angle	10

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335