

IR71 PAR38/SP



Description

120V 71W Spot EikON IR PAR38 Medium Base

Specifications

Bulb Type	PAR 38
Base Type	Medium Screw (E26)
Filament	CC-8
MOL in/mm	5.51/140
MOD in/mm	4.80/122
Volts	120
Watts	71
Lumens	1350
CT deg K	2850
Avg Life	4,000
Photo No	961
Approx Initial Max Beam CP	14000
Beam Angle	10

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335