



**Description**

120V 75W 12 Deg. Spot MR16 Front Glass Medium Base

Specifications	
<b>Bulb Type</b>	MR16
<b>Base Type</b>	Medium Screw (E26)
<b>Filament</b>	CC-8
<b>Special Desc</b>	Faceted Reflector w/ Front Glass
<b>MOL in/mm</b>	2.84/72.0
<b>MOD in/mm</b>	2.00/50.8
<b>Volts</b>	120
<b>Watts</b>	75
<b>CT deg K</b>	3000
<b>Avg Life</b>	2,000
<b>Type Use</b>	Display 12
<b>Photo No</b>	244
<b>Approx Initial Max Beam CP</b>	5000
<b>Beam Angle</b>	12
<b>Beam Description</b>	Spot
<b>Common Code</b>	JDR120V75WN/E26/FG

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335