



LED13W4PVL/835DR-G5

**Description**

3500K LED Litespan Direct Replacement 4-pin CFL 13W 900lm dim
Vertical long G24q Base 80+CRI 2BD

Specifications	
Base Type	G24q
Special Desc	NOT COMPATIBLE WITH ALL BALLASTS. SEE eiko.com FOR LIST OF TESTED BALLASTS.
Volts	120~277 VAC
Watts	13
Amps	0.13
Ambient Operating Temp Range	-20°C (-4°F) to 45°C (113°F)
Lumens	900
CT deg K	3500
Type Use	DIRECT REPLACEMENT FOR 26W,32W,42W 4-PIN G24q &GX2
Photo No	1047
CRI	80
Lumens per Watt	69.23000

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335