

LED-14-T1.75 WEDGE-W



Description

14VAC/DC T1-3/4 Wedge Base White

Specifications

Bulb Type	T-1 3/4
Base Type	Sub-Miniature Wedge (W2.1x4.6d)
MOL in/mm	0.77/19.4
MOD in/mm	0.22/5.5
Volts	14 VAC/DC
Lumens	1.1
mcd at 20ma	9000-12000
Avg Life	30,000
Photo No	612
Replaces	18, 37, 70, 73, 74
Led Type	Single
Emitted Color	White
Lens Color	Clear
Viewing Angle	100
mA	7.2

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335