

LED2WMR11/120/830-G5

Image Not Found

Description

LED GEN5 MR11 GU4, 120 deg beam, 2.5W - 140lm,
Non-Dimmable, 3000K, 80+CRI, 12VAC/DC

Specifications

Bulb Type	MR11
Base Type	GU4
MOL in/mm	1.44/36.5
MOD in/mm	1.38/35
Volts	12 VAC/DC
Watts	2.5
Ambient Operating Temp Range	-20°C (-4°F) to 40°C (104°F)
Lumens	140
CT deg K	3000
Avg Life	35,000
Photo No	1060
Beam Angle	120
CRI	80

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335