

# LED4WMR11/120/830-G5

Image Not Found

**Description**

LED GEN5 MR11 GU4, 120 deg beam, 4W - 160lm, Non-Dimmable, 3000K, 80+CRI, 12VAC/DC

**Specifications**

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Bulb Type</b>                    | MR11                         |
| <b>Base Type</b>                    | GU4                          |
| <b>MOL in/mm</b>                    | 1.61/40.9                    |
| <b>MOD in/mm</b>                    | 1.38/35                      |
| <b>Volts</b>                        | 12 VAC/DC                    |
| <b>Watts</b>                        | 4                            |
| <b>Ambient Operating Temp Range</b> | -20°C (-4°F) to 40°C (104°F) |
| <b>Lumens</b>                       | 160                          |
| <b>CT deg K</b>                     | 3000                         |
| <b>Avg Life</b>                     | 35,000                       |
| <b>Photo No</b>                     | 1061                         |
| <b>Beam Angle</b>                   | 120                          |
| <b>CRI</b>                          | 80                           |

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335