



Description 150W HPS ED23-1/2 Mogul Base

Specifications

Bulb Type	ED-23.5
Base Type	Mogul Screw (E39)
MOL in/mm	7.75/196.9
MOD in/mm	2.95/75.0
LCL in/mm	5.00/127.0
Volts	55
Watts	150
CT deg K	2100
Avg Life	24,000
Photo No	293
Common Code	C150S55
ANSI Ballast	S55
CRI	21
Burning Position	Universal
Approx Initial Lumens	16000
Approx Mean Lumens	14400
Fixt Rqmt	Open
Coating	Clear
Approvals	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335