



Description

150W ED-17 Medium Base Pulse Start Universal Burn

Specifications

Bulb Type	ED-17
Base Type	Medium Screw (E26)
Special Desc	Pulse Start
MOL in/mm	5.50/139.7
MOD in/mm	2.13/54.0
LCL in/mm	3.44/87.3
Watts	150
CT deg K	4000
Avg Life	15,000
Photo No	300
Common Code	MVR150/U/MED
ANSI Ballast	M102/M142
CRI	70
Burning Position	Universal
Approx Initial Lumens	14000
Approx Mean Lumens	10500
Fixt Rqmt	Enclosed
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335