



MH-DE150/TD/UVS/4K



Description

150W 4000K T7 RSC Double Ended Base

Specifications	
Bulb Type	T-7
Base Type	Recessed Single Contact (R7s)
Special Desc	Pulse Start & UV Shielded
MOL in/mm	5.19/131.8
Watts	150
CT deg K	4200
Avg Life	10,000
Photo No	302
Common Code	HQI-DE 150/NDX
ANSI Ballast	M81/M102/M142
CRI	70
Burning Position	Hor +/-45
Approx Initial Lumens	11250
Approx Mean Lumens	8400
Fixt Rqmt	Enclosed
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335