



MH-DE70/TD/UVS/3K



Description

70W 3000K UV Shield T6 RSC Double Ended Base

Specifications	
Bulb Type	T-6
Base Type	Recessed Single Contact (R7s)
Special Desc	Pulse Start & UV Shielded
MOL in/mm	4.50/114.3
Watts	70
CT deg K	3000
Avg Life	10,000
Photo No	301
Common Code	HQI-DE 70/WDX
ANSI Ballast	M85/M98
CRI	70
Burning Position	Hor +/-45
Approx Initial Lumens	5200
Approx Mean Lumens	3400
Fixt Rqmt	Enclosed
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335