



Q1000T3/CL/120V



Description

120V 1000W T3 R7S Base Double Ended

Specifications

Bulb Type	T-3
Base Type	Recessed Single Contact (R7s)
Filament	C-8
MOL in/mm	10.06/255.6
MOD in/mm	0.40/10.0
Volts	120
Watts	1000
Lumens	22000
CT deg K	2900
Avg Life	2,000
Type Use	General
Photo No	258
Burning Position	HOR

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335