



Description

120V 100W T-4 DC Bayonet Base

Specifications

Bulb Type	T-4
Base Type	DC Bayonet (BA15d)
Filament	CC-8
MOL in/mm	2.44/61.9
MOD in/mm	0.52/13.0
LCL in/mm	1.38/34.9
Volts	120
Watts	100
Lumens	1500
CT deg K	2900
Avg Life	2,000
Type Use	General
Photo No	227

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335