



Q150W/S130V

**Description**

130V 150W T-2 3/4 R7s Base Double Ended

Specifications

Bulb Type	T-2 3/4
Base Type	Recessed Single Contact (R7s)
Filament	C-8
MOL in/mm	3.15/80.0
MOD in/mm	0.344/8.74
Volts	130
Watts	150
Lumens	2200
CT deg K	2850
Avg Life	2,000
Type Use	General
Photo No	258

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335