



**Description**

130V 250W Frosted T-4 DC Bayonet Base

Specifications	
<b>Bulb Type</b>	T-4
<b>Base Type</b>	DC Bayonet (BA15d)
<b>Filament</b>	CC-8
<b>MOL in/mm</b>	3.00/76.2
<b>MOD in/mm</b>	0.52/13.0
<b>LCL in/mm</b>	1.62/41.0
<b>Volts</b>	130
<b>Watts</b>	250
<b>Lumens</b>	4800
<b>CT deg K</b>	3000
<b>Avg Life</b>	2,000
<b>Type Use</b>	General
<b>Photo No</b>	228
<b>Coating</b>	Frosted

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335