

# Q400W/S130V



**Description**

130V 400W T-3 1/4 R7s Base Double Ended

Specifications	
<b>Bulb Type</b>	T-3 1/4
<b>Base Type</b>	Recessed Single Contact (R7s)
<b>Filament</b>	C-8
<b>MOL in/mm</b>	3.15/80.0
<b>MOD in/mm</b>	0.406/10.32
<b>Volts</b>	130
<b>Watts</b>	400
<b>Lumens</b>	5500
<b>CT deg K</b>	2850
<b>Avg Life</b>	2,000
<b>Type Use</b>	General
<b>Photo No</b>	258

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335