



**Description**

13W Quad-Tube 2700K GX23-2 Base Fluorescent

**Specifications**

<b>Bulb Type</b>	T-4
<b>Base Type</b>	GX23-2
<b>MOL in/mm</b>	4.6/117
<b>Volts</b>	120
<b>Watts</b>	13
<b>CT deg K</b>	2700
<b>Avg Life</b>	10,000
<b>Photo No</b>	368
<b>CRI</b>	82
<b>Approx Initial Lumens</b>	810
<b>Approx Mean Lumens</b>	685
<b>Approvals</b>	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335