



Description

26W Quad-Tube 5000K G24q3 4 Pin Base Fluorescent

Specifications

Bulb Type	T-4
Base Type	G24q-3
MOL in/mm	6.4/163
Watts	26
CT deg K	5000
Avg Life	10,000
Photo No	434
CRI	82
Approx Initial Lumens	1710
Approx Mean Lumens	1460
Approvals	TCLP Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335