



**Description**

105W 120V Spiral 5000K Medium Base

**Specifications**

<b>Base Type</b>	Medium Screw (E26)
<b>Special Desc</b>	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
<b>MOL in/mm</b>	10.75/273
<b>MOD in/mm</b>	4.02/102
<b>Volts</b>	120
<b>Watts</b>	105
<b>Ambient Operating Temp Range</b>	Max ambient temp 104°F. Open socket type fixture.
<b>CT deg K</b>	5000
<b>Avg Life</b>	10,000
<b>Photo No</b>	848
<b>Replaces</b>	Std 420W Incandescent
<b>CRI</b>	>80
<b>Approx Initial Lumens</b>	6600
<b>Approvals</b>	UL/CSA, TCLP Compliant

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335