



Description

13W 120V 5000K Spiral Shaped

Specifications

Base Type	Medium Screw (E26)
Special Desc	Not for use with dimmers, electronic timers, photocells, or motion/occupancy sensors.
MOL in/mm	4.10/104
MOD in/mm	1.97/50.0
Volts	120
Watts	13
Ambient Operating Temp Range	-18°C (0°F) to 40°C (104°F)
CT deg K	5000
Avg Life	10,000
Photo No	558
Replaces	Std 60W Incandescent
CRI	82
Approx Initial Lumens	800
Approvals	UL/CSA, TCLP Compliant, RoHS, Energy Star

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335