



Description 18W 120V 4100K Spiral Shaped

Specifications

Base Type	Medium Screw (E26)
Special Desc	Not for use with dimmers, electronic timers, photocells, or motion/occupancy sensors.
MOL in/mm	4.528/115
MOD in/mm	2.126/54
Volts	120
Watts	18
Ambient Operating Temp Range	-18°C (0°F) to 50°C (122°F)
CT deg K	4100
Avg Life	10,000
Photo No	559
Replaces	Std 75W Incandescent
CRI	80
Approx Initial Lumens	1200
Approvals	UL/cUL, TCLP Compliant, RoHS

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335