



Description 26W 120V 2700K Spiral Shaped

Specifications

Base Type	Medium Screw (E26)
MOL in/mm	5.079/129
MOD in/mm	2.126/54
Watts	26
Ambient Operating Temp Range	-18°C (0°F) to 50°C (122°F)
CT deg K	2700
Avg Life	10,000
Photo No	636
Replaces	Std 110W Incandescent
CRI	80
Approx Initial Lumens	1700
Approvals	UL/CSA, TCLP Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335