

## TR14D3E Product Details



**TR14D3E**

(1-1423393-6)

TE Internal Number: 1-1423393-6

**Active**

### Time Delay Relays

[Not reviewed for RoHS Compliance](#)

#### Product Highlights:

- TR - Control Relay - Timing Version Series
- Input Voltage = 215 VDC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 10A
- Mounting Options = Socket

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) | 
 [Request Sample](#) | 
 [Find Similar Products](#) | 
 [Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul>	<p><b>Additional Information:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Product Line Information</a></li> </ul> <p><b>Additional Product Images:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Wiring Diagram</a></li> </ul> <p><b>Related Products:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> </ul>

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"> <li>• Termination Type = 16 Flat Base Pins</li> <li>• Magnetic Blow-Out Device = Without</li> </ul> <p><b>Electrical Characteristics:</b></p> <ul style="list-style-type: none"> <li>• Input Voltage (VDC) = 215</li> <li>• Contact Rating = 10A</li> </ul> <p><b>Body Related Features:</b></p> <ul style="list-style-type: none"> <li>• Series = TR - Control Relay - Timing Version</li> </ul> <p><b>Contact Related Features:</b></p> <ul style="list-style-type: none"> <li>• Mounting Options = Socket</li> <li>• Mode of Operation = Delay on Energization</li> <li>• Delay Time = 4 seconds to 120 seconds</li> <li>• Type of Control = Potentiometer Adjustable</li> <li>• Repeatability, Max. = ? 2%</li> <li>• Approved Standards = CSA Certified, UL Listed</li> <li>• Contact Base Material = Silver Plated</li> <li>• Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]</li> </ul>	<p><b>Configuration Related Features:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Contact Arrangement</a> = 4 Form C, 4PDT, 4 C/O</li> <li>• Multiple Timing Ranges = Without</li> </ul> <p><b>Industry Standards:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">RoHS/ELV Compliance</a> = Not reviewed for ELV/RoHS compliance</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not reviewed for lead free solder process</li> </ul> <p><b>Conditions for Usage:</b></p> <ul style="list-style-type: none"> <li>• Temperature Range (?C) = 0 - 50</li> </ul> <p><b>Other:</b></p> <ul style="list-style-type: none"> <li>• Brand = Agastat</li> </ul>

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)