



Professionally approved products.

Datasheet

10m Long 94 bar Copper Tubing, -50 → +200°C

RS Stock number 0846480



Features

Standard Duty, Annealed Copper Tube
Annealed, standard duty copper tube
Use with Enots compression fittings
Operating Temperature Range -50 → +200 °C
CW024A grade