

Professionally approved products.

Datasheet

10m Long 128 bar Copper Tubing, -50 → +200°C

RS Stock number 846503



Features

Standard Duty, Annealed Copper Tube
Annealed, standard duty copper tube
Use with Enots compression fittings
Operating Temperature Range -50 → +200 °C
CW024A grade

Standards:BS 12449

Copper Tubing
Length: 10m
Maximum Operating Pressure: 128 bar
Maximum Operating Temperature: +200°C
Minimum Operating Temperature: -50°C
Tube Inside Diameter: 2.8mm
Tube Outside Diameter: 4mm